

TECHNICAL DATASHEET



Short protective hood CA-1 Plus

Short protective hood with air distribution



Description

Light hood CA-1 provides sufficient protection of the breathing paths and protect the foreface against dust and other contaminants..

Application

This short light hood is an optimal solution for protection of breath and face in dusty environments where no further mechanical protection is required.



Techware Pty Ltd
ABN: 13 914 775 899
Phone: 1300 062 947
Email: sales@maxisafe.com.au
Website: www.maxisafe.com.au

Techware Pty Ltd
PO Box 4220
Hoppers Crossing
VIC 3029
Australia

DA-002_-_720112_-_CA-1Plus_-_EN

© CleanAIR® All rights reserved

Revision: 2021_04_19
Output: 2021_04_19

TECHNICAL DATASHEET

Short protective hood CA-1 Plus

Short protective hood with air distribution



Technical specification

Product code	72 01 12 (orange); 72 01 12B (blue)		
Weight	150 g		
Dimensions	280 mm / 210 mm / 270 mm		
Materials	Visor: cellulose propionate Textile part: laminated polyethylene (PP+PE) Head harness: polypropylene		
Input air distribution connection	QuickLOCK™		
Standard	EN 12941	EN 14594	EN 166
Protection class / NPF***	TH3 / 500	3A / 200	1SF
Storage conditions	– 10°C to + 55°C, humidity 20 - 95 % Rh		
Operating conditions	0°C to + 60°C, humidity 20 - 95 % Rh		

Compatible powered air purifying respirators / airline systems

Standard / Class

CleanAIR® Basic	EN 12 941 / TH3
CleanAIR® Basic 2000 Flow Control	EN 12 941 / TH3
CleanAIR® AerGO®	EN 12 941 / TH3
CleanAIR® Chemical 2F Plus	EN 12 941 / TH3
CleanAIR® Chemical 3F Plus	EN 12 941 / TH3
CleanAIR® MedicAER	EN 12 941 / TH3
CleanAIR® Pressure Flow Master	EN 14594 / 3A

Compatible accessories and spare parts

Product code

Headband for light headtops	72 00 01
Sweatband for light headtops - pack of 5 pcs	16 70 03/5
Protection foil – 10 pcs	70 01 20/10
Winter cap + sweatband	71 01 10
Light flexi hose QuickLOCK™	71 00 60

Disclaimer Notice

All the information contained herein is believed to be accurate and is subject to change without notice. Users should independently evaluate the suitability of each product for their own applications. CleanAIR® products are not designed for, and may not be used in, all applications.